




# SPA-TP Plastic Cross Recessed Pan Head Tapping Screws - RENY

Lightweight High Specific Strength



## Material/Finish



SPA-TP	
Main Body	RENY™*1 (50% Glass Fiber Reinforced Polyamide MXD6) (Ivory)
Heat Resistance Temperature*2	105°C

- \*1: RENY™ is a trademark or registered trademark of Mitsubishi Gas Chemical Company, Inc.
- \*2: This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

- RENY™ Phillips cross recessed pan head tapping screws.
- RENY™ is a thermoplastic engineering plastic with excellent tensile and bending strength.
- It is highly fatigue-resistant and has excellent creep and heat insulation properties.
- While it is nearly as strong as metal, its weight is approximately 1/5 of iron.
- For the properties and precautions for use of plastic screws, see "Properties of Plastic Screws."

## Application

Heat insulation and dew condensation prevention of refrigerating and freezing facilities  
Electrical and electronic equipment / Offshore instruments / Plating facilities

Unit : mm

Part Number ◀1	Nominal of Thread	L ◀2	D1	L1	Cross-recessed Socket No.	Mass (g)	Qty per Pack
SPA-M3-TP	M3	8 10	5.5	2	2	0.17 - 0.19	20
SPA-M3-TP(100)	M3	8 10	5.5	2	2	0.17 - 0.19	100
SPA-M3-TP(1000)	M3	8 10	5.5	2	2	0.17 - 0.19	1000
SPA-M4-TP	M4	8 10	7	2.6	2	0.22 - 0.25	20
SPA-M4-TP(100)	M4	8 10	7	2.6	2	0.22 - 0.25	100
SPA-M4-TP(1000)	M4	8 10	7	2.6	2	0.22 - 0.25	1000

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

## Part Number Specification

### SPA-M3-8-TP



1 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available