


# SNZ3S Cross Recessed Micro Pan Head Machine Screws - Type 0 - 3



Miniature Size **SUS** Stainless steel



● Material/Finish



	<b>SNZ3S</b>
Main Body	Stainless Steel

- Miniature screws for precision instruments (Type 0 - 3).
- M1.4 - M2.6.
- Pan head machine screw type with low head height. For applications with limited overhead space.

● Application

For making devices and equipment more compact  
Compact precision equipment

Unit : mm

Part Number	M (Coarse)		L										D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	2	2.5	3	3.5	4	5	6	8	10	12						
<b>SNZ3S-M1.4</b>	M1.4	0.3	2	2.5	3	3.5	4	5	6	8	10	12	2.5	0.8	0	0.07	0.04 - 0.13	50
<b>SNZ3S-M1.6</b>	M1.6	0.35	2	2.5	3	3.5	4	5	6	8	10		2.8	0.85	0	0.1	0.05 - 0.14	50
<b>SNZ3S-M1.7</b>	M1.7	0.35	2	2.5	3	3.5	4	5	6	8	10	12	3.0	0.9	0	0.14	0.06 - 0.18	50
<b>SNZ3S-M2</b>	M2	0.4	2	2.5	3	3.5	4	5	6	8	10	12	3.5	1.0	0	0.22	0.09 - 0.3	50
<b>SNZ3S-M2.6</b>	M2.6	0.45			3		4		6	8			4.5	1.2	0	0.53	0.21 - 0.36	50

\*1 : Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

**SNZ3S-M2-3**



<b>1</b> Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Available / Add'l charge	Not Available