




SPC-N-WH Plastic Hex Nuts - PC

Lightweight Electrical Insulation



- PC (polycarbonate) hex nuts.
- PC (polycarbonate) has the highest shock resistance of engineering plastics.
- Allowable operating temperature*1 (min./max.): -40°C/115°C
- PC has low water absorbency and excellent weather resistance.
- For the properties and precautions for use of plastic screws, see "Properties of Plastic Screws."

● Application

Electrical and electronic equipment

● Material/Finish



| | SPC-N-WH |
|-------------------------------|----------------------------|
| Main Body | PC (Polycarbonate) (White) |
| Heat Resistance Temperature*1 | 115°C |

*1 : This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

Unit : mm

| Part Number | M (Coarse) | | B | T | Mass (g) | Qty per Pack |
|-------------------|-------------------|-------|----|-----|----------|--------------|
| | Nominal of Thread | Pitch | | | | |
| SPC-M8-N-WH | M8 | 1.25 | 13 | 6.5 | 0.8 | 20 |
| SPC-M8-N-WH(250) | M8 | 1.25 | 13 | 6.5 | 0.8 | 250 |
| SPC-M10-N-WH | M10 | 1.5 | 17 | 8 | 1.7 | 20 |
| SPC-M10-N-WH(200) | M10 | 1.5 | 17 | 8 | 1.7 | 200 |
| SPC-M12-N-WH | M12 | 1.75 | 19 | 10 | 2.6 | 10 |
| SPC-M12-N-WH(100) | M12 | 1.75 | 19 | 10 | 2.6 | 100 |
| SPC-M16-N-WH | M16 | 2 | 24 | 13 | 3.6 | 5 |
| SPC-M16-N-WH(50) | M16 | 2 | 24 | 13 | 3.6 | 50 |

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SPC-M10-N-WH



| | | | | |
|--------------------------|----------------------------|-------------------------|---------------------|--------------------------------------|
| Individual Sales | Cleanroom Wash & Packaging | Screw Length Adjustment | Vibration Resistant | Modification process for captive use |
| Available / Add'l charge | Available / Add'l charge | Not Available | Not Available | Not Available |