


SNSS-FC Hex Socket Head Cap Screws - Fluorine Coating



Seizing Prevention SUS Stainless steel



● Material/Finish




	SNSS-FC
Main Body	SUSXM7 (S.S. Grade : A2) Fluorine Coating
Strength Class	A2-70

● Tightening property (reference)

Part Number : SNSS-M5 - 25-FC

➡ P.xxxx





- Coating with good cost performance.
- Excellent lubricating ability and suitable for seizing prevention of screws.
- Complies with JIS B 1176, ISO 4762, and DIN 912. For details on shape and dimensions, please refer to the "Technical Information (JIS B 1176, ISO 4762)".

● Application

Seizing prevention
FPD production equipment, semiconductor devices,
and general industrial machines

Unit : mm

Part Number	M (Coarse)		L 												D1	L1	B	Mass (g)	Qty per pack
	Nominal of Thread 	Pitch																	
SNSS-M3-FC	M3	0.5	5	6	8	10	12	16	20					5.5	3	2.5	0.67 - 1.4	10	
SNSS-M4-FC	M4	0.7		6	8	10	12	16	20	25				7	4	3	1.5 - 3.2	10	
SNSS-M5-FC	M5	0.8			8	10	12	16	20	25				8.5	5	4	2.5 - 4.8	10	
SNSS-M6-FC	M6	1				10	12	16	20	25	30			10	6	5	4.7 - 8.3	10	
SNSS-M8-FC	M8	1.25						16	20	25	30	35		13	8	6	12 - 19	10	
SNSS-M10-FC	M10	1.5							20	25	30	35	40	16	10	8	23 - 33	10	

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part number specification

SNSS-M5-16-FC

Product Code



Product Code

Individual Sales ➡ P.xxxx	Cleanroom Wash & Packaging ➡ P.xxxx	Screw Length Adjustment ➡ P.xxxx	Vibration Resistant ➡ P.xxxx	Modification process for captive use ➡ P.xxxx
Available / Add'l charge	Not Available	Not Available	Not Available	Please feel free to contact us