



- Set of Flat Head Bolt with Hexalobular Socket\*1 **SRFXS** (→ P.xxxx) and Rosette Washer **SWAS-RW** (→ P.xxxx).
- **SRFXS** can be used without countersinking.
- **SRFXS** cannot be mounted or removed by normal tools. Since the combined use of **SWAS-RW** will disable pinching and rotating **SRFXS** directly, the anti-theft performance is improved.
- Install and remove with **SRX** Dedicated Wrench or **SRXB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.
- \*1: The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

#### Application


Machinery / Tools / Equipment / Devices disassembly prevention / Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures / Decoration / Prevention from getting caught

	M (Coars	(م:															Annlicabl	e Bit Type			Unit: mm
Part Number 1	Nominal of Thread	1	L◀	<b>4</b> 2				D1	D1 L1		D d		Applicable Wrench Type		Driver	Hexalobular Socket No.	Mass (g)	Qty per Pack			
SRFXS-M3-SET	M3	0.5	6	8	10	12					6	1.75	10	3.5	2	SRX-10	SRXB-10	SRD-6.35	10	1.3 - 1.5	10
SRFXS-M4-SET	M4	0.7		8	10	12	16	20			8	2.3	12	4.5	2.5	SRX-20	SRXB-20	SRD-6.35	20	2.2 - 3.1	10
SRFXS-M5-SET	M5	8.0			10	12	16	20	25		10	2.8	14	5.5	3	SRX-25	SRXB-25	SRD-6.35	25	4 - 5.9	10
SRFXS-M6-SET	M6	1			10	12	16	20	25	30	12	3.4	16	6.5	3.5	SRX-30	SRXB-30	SRD-6.35	30	6.4 - 10	10

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.


## • SRX Dedicated Wrench

			Unit:mm
Part Number	L <sub>1</sub>	L2	Mass (g)
SRX-10	60	20	3.7
SRX-20	67	23	8.2
SRX-25	70	25	11
SRX-30	81	28	20




#### • SRXB Bit Part No.

Part Number	Mass (g)
SRXB-10	4.36
SRXB-20	4.57
SRXB-25	4.79
SRXB-30	5.50



## • SRD Dedicated magnet screwdriver

2 0 0 11		50.0	Unit:mm
Part Number	L	В	Mass(g)
SRD-6.35	210	6.35	98






# SRGS Button Head Cap Screws with Five - Lobe Holes (with Pin)



Unit: mm









#### Material/Finish



	SRGS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

- Button head cap screws with a pin at the center of the five slots, inspired by plum blossoms. Also suitable for decorative uses.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRGB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.

#### Application

Machinery / Tools / Equipment / Devices disassembly prevention/ tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

Part Number 1	M (Coarse) Nominal of Thread	Pitch	L	2									D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty per pack
SRGS-M3	M3	0.5	6	8	10	12	16	20					5.7	1.65	SRGB-3	SRD-6.35	0.43 - 1	10
SRGS-M4	M4	0.7	6	8	10	12	16	20	25	30	40		7.6	2.2	SRGB-4	SRD-6.35	0.88 - 3.4	10
SRGS-M5	M5	0.8			10	12	16	20	25	30	40		9.5	2.75	SRGB-56	SRD-6.35	2.1 - 5.7	10
SRGS-M6	M6	1			10	12	16	20	25	30	40	50	10.5	3.3	SRGB-56	SRD-6.35	3.2 - 10	10
SRGS-M8	M8	1.25					16	20	25	30	40	50	14	4.4	SRGB-8	SRD-6.35	8.2 - 19	5


• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.


## SPGR Dedicated hits

SKGD Deute	ated bits	Unit: mm						
Part Number	L	В	Mass (g)					
SRGB-3	32	6.35	6					
SRGB-4	32	6.35	7.1					
SRGB-56	32	6.35	7.5					
SRGB-8	32	6.35	8.2					










SRD Dedicated magnet screwdriver

			Unit : mm
Part Number	L	В	Mass (g)
SRD-6.35	210	6.35	98






















# **SRHFS** Hex Socket Flat Head Bolts (with Pin)





Strength Class





Material/Finish	♠ RoHS
	SRHFS
Main Body	Equivalent to SUS304

Equivalent to A2-50



- Flat head bolts with pin at the center of their
- This prevents mounting and removing with regular
- Install and remove with **SRH** Dedicated Wrench or **SRHB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.

### Application


Machinery / Tools / Equipment / Devices disassembly prevention/ Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

																						Unit: mm
M (Coarse)										Applicable	Applicabl	e Bit Type			Ottv							
Part Number 1	Nominal of Thread	Pitch	L◀	. •2										D1 L1		В	Wrench Type	Bit	Driver	Mass (g)		Qty per Pack
SRHFS-M3	M3	0.5	6	8	10	12	16	20	25					6	1.75	2	SRH-2	SRHB-2	SRD-6.35	0.53	- 1.4	10
SRHFS-M4	M4	0.7		8	10	12	16	20	25	30				8	2.3	2.5	SRH-2.5	SRHB-2.5	SRD-6.35	1.2	- 2.9	10
SRHFS-M5	M5	0.8		8	10	12	16	20	25	30		40	50	10	2.8	3	SRH-3	SRHB-3	SRD-6.35	2.3	- 7.4	10
SRHFS-M6	M6	1			10	12	16	20	25	30	35	40	50	12	3.4	4	SRH-4	SRHB-4	SRD-6.35	3.9	- 12	10
SRHFS-M8	M8	1.25			10	12	16	20	25	30	35	40	50	16	4.7	5	SRH-5	SRHB-5	SRD-6.35	9	- 23	10
SRHFS-M10	M10	1.5							25	30		40		18.3	5.6	6	SRH-6	SRHB-6	SRD-6.35	19	- 29	10

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

# • SRH Dedicated Wrench


				Unit:mm
Part Number	В	L1	L2	Mass (g)
SRH-2	2	50	16	1.8
SRH-2.5	2.5	56	18	3.1
SRH-3	3	63	20	5
SRH-4	4	70	25	10
SRH-5	5	80	28	18
SRH-6	6	90	32	35



# • SRHB Bit Part No.

Unit	: mn
------	------

Part Number	В	Mass (g)
SRHB-2	2	4.81
SRHB-2.5	2.5	4.93
SRHB-3	3	4.85
SRHB-4	4	6.31
SRHB-5	5	5.51
SRHB-6	6	5.98




### • SRD Dedicated magnet screwdriver

Ur	iit	:	m	m

Part Number	L	В	Mass (g)
SRD-6.35	210	6.35	98













# SRTRS Triangular Socket Button Head Cap Screws











#### Material/Finish



	SRTRS
本体	SUS304相当
強度区分	A2-50相当



- Button head cap screws with triangular socket.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRTRB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.
- Application

Machinery / Tools / Equipment / Devices disassembly prevention/ Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

Unit:mm

Part Number	M (Coarse)		. 4	L <b>1</b> 2				D <sub>1</sub>	D1 L1 t		Bit	Screwdriver	Mass	Qty		
<b>41</b>	Nominal of Thread	Pitch	L	_						Di	Li		Part No.	Part No.	(g)	per Pack
SRTRS-M3	M3	0.5	6	8	10	12	16	20		5.7	1.65	0.95	SRTRB-3	SRD-6.35	0.43 - 1.1	10
SRTRS-M4	M4	0.7	6	8	10	12	16	20		7.6	2.2	1.3	SRTRB-4	SRD-6.35	0.89 - 2	10
SRTRS-M5	M5	8.0			10	12	16	20	25	9.5	2.75	1.5	SRTRB-5	SRD-6.35	2.1 - 4.1	10
SRTRS-M6	M6	1		8	10	12	16	20	25	10.5	3.3	1.8	SRTRB-6	SRD-6.35	2.5 - 5.9	10

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

#### SRTRB Dedicated bits

		SRT
		SKI






- ORTHODO	Unit: mm		
Part Number	L	В	Mass (g)
SRTRB-3	32	6.35	5.8
SRTRB-4	32	6.35	6.4
SRTRB-5	32	6.35	6.5
SRTRB-6	32	6.35	7

### • SRD Dedicated magnet screwdriver

U	n	it	:	m


Part Number	L	В	Mass (g)
SRD-6.35	210	6.35	98























## e-nedzi.com


# SRTS Two Hole Pan Head Machine Screws













- This prevents mounting and removing with regular
- Install and remove with **SRTB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.
- The simple head design is suitable for decoration.
- Application

Machinery / Tools / Equipment / Devices disassembly prevention/ Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

#### Material/Finish



	SRTS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

Unit:mm


Part Number	M (Coarse)		. 4	L <b>2</b>			D.	Bit S		Screwdriver	Mass	Qty		
<b>41</b>	Nominal of Thread	Pitch	_				D1	L1	Part No.	Part No.	(g)	per Pack		
SRTS-M3	M3	0.5	6	8	10				6	1.8	SRTB-4	SRD-6.35	0.66 - 0.82	20
SRTS-M4	M4	0.7			10	12	16		8	2.4	SRTB-8	SRD-6.35	1.7 - 2.2	20
SRTS-M5	M5	0.8				12	16	20	10	3	SRTB-10	SRD-6.35	3.4 - 4.3	20

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

### • SRTB Dedicated bit

Unit:mm


Part Number	L	В	Mass (g)
SRTB-4	25.4	6.35	5
SRTB-8	25.4	6.35	5
SRTB-10	25.4	6.35	5.2






			Unit : mm
Part Number	L	В	Mass (g)
SRD-6.35	210	6.35	98




















# SRWFS Triwing Flat Head Machine Screws









#### Material/Finish



	SRWFS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50



- This prevents mounting and removing with regular tools.
- Install and remove with **SRWB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.

#### Application

Machinery / Tools / Equipment / Devices disassembly prevention/ Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures


Unit:mm

Part Number	Part Number M (Coarse)													D1	L <sub>1</sub>	Bit	Screwdriver	Mass		Qty
<b>1</b>	Nominal of Thread	Pitch	-	_										D1		Part No.	Part No.	(g)		per Pack
SRWFS-M2	M2	0.4	5	6	8									3.8	1.2	SRWB-1	SRD-6.35	0.16 -	0.21	10
SRWFS-M3	M3	0.5		6	8	10	12	16	20	25				5.5	1.65	SRWB-2	SRD-6.35	0.53 -	1.4	10
SRWFS-M4	M4	0.7		6	8	10	12	16	20	25	30			8.4	2.7	SRWB-4	SRD-6.35	1.1 -	2.9	10
SRWFS-M5	M5	8.0				10	12	16	20	25	30	40	50	9.3	2.7	SRWB-5	SRD-6.35	2.5 -	7.4	10
SRWFS-M6	M6	1				10	12	16	20	25	30	40	50	11.3	3.3	SRWB-6	SRD-6.35	3.9 -	12	10
SRWFS-M8	M8	1.25						16	20	25	30	40	50	15.8	4.65	SRWB-7	SRD-6.35	11 -:	23	10

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

### • SRWB Dedicated bit

Unit:mm








• SRD Dedicated magnet screwdriver


Unit:mm


			Omerm
Part Number	L	В	Mass (g)
SRD-6.35	210	6.35	98




















### e-nedzi.com<sup>®</sup>


# SRWS Triwing Pan Head Machine Screws













- This prevents mounting and removing with regular tools.
- Install and remove with **SRWB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.

#### Application

Machinery / Tools / Equipment / Devices disassembly prevention/ Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

#### Material/Finish



		~	10115
	SRWS		
Main Body	Equivalent to SUS304		
Strength Class	Equivalent to A2-50		

Unit:mm


Part Number 1	M (Coarse)	L <b>€</b> 2					D <sub>1</sub>	L	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty	
rait Number	Nominal of Thread	Pitch	_	_		D1 L1 Bit		Bit Fait No. Sciewanie Fait No.		iviass (g)	per Pack		
SRWS-M3	M3	0.5	6	8	10			5.6	1.8	SRWB-2	SRD-6.35	0.54 - 0.7	20
SRWS-M4	M4	0.7		8	10	12		8.2	2.9	SRWB-4	SRD-6.35	1.5 - 1.9	20
SRWS-M5	M5	0.8			10	12	16	9.5	3.4	SRWB-5	SRD-6.35	2.8 - 3.5	20


• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

### • SRWB Dedicated Bit

Unit:mm

			011101111111
Part Number	L	В	Mass (g)
SRWB-2	25.4	6.35	4.8
SRWB-4	25.4	6.35	5.2
SRWB-5	25.4	6.35	5.6






Unit:mm

Part Number	L	В	Mass (g)
SRD-6.35	210	6.35	98


























# Button Head Cap Screws with Three - Lobe Holes (with Pin)









#### Material/Finish



	SRSAS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50



- Button head cap screws with pin at the center of the three groove holes.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRSAB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.
- Application

Machinery / Tools / Equipment / Devices disassembly prevention/ Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures


Unit:mm

Part Number	M (Coarse)		L						D1 L1	La		Bit	Screwdriver	Mass	Qty				
<b>1</b>	Nominal of Thread	Pitch											וט	L1	١	Part No.	Part No.	(g)	per Pack
SRSAS-M3	M3	0.5	6	8	10	12	20						5.7	1.65	0.9	SRSAB-3	SRD-6.35	0.43 - 1.1	10
SRSAS-M4	M4	0.7	6	8	10	12	20	16	25	30			7.6	2.2	1.3	SRSAB-4	SRD-6.35	0.89 - 2.7	10
SRSAS-M5	M5	8.0		8	10	12	20	16	25	30	40		10.5	3.3	1.6	SRSAB-56	SRD-6.35	2.4 - 6.6	10
SRSAS-M6	M6	1			10	12	20	16	25	30	40	50	10.5	3.3	1.6	SRSAB-56	SRD-6.35	3.2 - 11	10
SRSAS-M8	M8	1.25				12	20	16	25	30	40	50	14	4.4	2.5	SRSAB-8	SRD-6.35	7.2 - 19	10

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

#### • SRSAB Dedicated bits


			Unit - mm
Part Number	L	В	Mass (g)
SRSAB-3	32	6.35	5.9
SRSAB-4	32	6.35	7
SRSAB-56	32	6.35	7.3
SRSAB-8	32	6.35	8.3



• SRD D	edicated ma	gnet screwdri	ver <sub>Unit:m</sub>
Part Numb	er L	В	Mass (g)
SRD-6 35	210	6 35	98



SRD



### Related Products

Install and remove with SRSAB Dedicated Bits and SRD Dedicated Magnetic Screwdriver together.




**Dedicated Magnet Screwdrivers** SRD



• Part number specification

Available / Add'l charge | Available / Add'l charge











# **SRHS** Socket Head Cap Screws with Hexalobular Socket and Pin











- Button head cap screws with pin at the center of their socket.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRH** Dedicated Wrench or **SRHB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.

### Application


Equipment/devices disassembly/tampering prevention Theft prevention for outdoor facilities Security measures Safety measures

																	Unit:mm
Part Number	M (Coarse)		. 4	2						D1 L1 B		В	Applicable	Applicable	Bit Type	Mass (g)	Qty
rait Nullibel	Nominal of Thread	Pitch	_	. 12				ם נו		Ь	Wrench Type	Bit	Driver	Mass (g)	per Pack		
SRHS-M3	M3	0.5	6	8	10	12	16			5.7	1.65	2	SRH-2	SRHB-2	SRD-6.35	0.48 - 0.93	20
SRHS-M4	M4	0.7	6	8	10	12	16	20		7.6	2.2	2.5	SRH-2.5	SRHB-2.5	SRD-6.35	1.1 - 2.2	20
SRHS-M5	M5	0.8		8	10	12	16	20		9.5	2.75	3	SRH-3	SRHB-3	SRD-6.35	1.8 - 3.3	20
SRHS-M6	M6	1			10	12	16	20	25	10.5	3.3	4	SRH-4	SRHB-4	SRD-6.35	3.3 - 6.1	10

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.


# • SRH Dedicated Wrench

				Unit:mm
Part Number	В	L1	L <sub>2</sub>	Mass (g)
SRH-2	2	50	16	1.8
SRH-2.5	2.5	56	18	3.1
SRH-3	3	63	20	5
SRH-4	4	70	25	10



### • SRHB Bit Part No.


		Unit : mm
Part Number	В	Mass (g)
SRHB-2	2	4.81
SRHB-2.5	2.5	4.93
SRHB-3	3	4.85
SRHB-4	4	6.31



# • SRD Dedicated Magnet Screwdriver

Unit	:	mm

Part Number	L	В	Mass (g)
SRD-6.35	210	6.35	98






# **SRFXS** Flat Head Screws with Hexalobular Socket and Pin









Material/Finish		RoHS
	SRFXS	
Main Body	Equivalent to SUS304	
Strength Class	Equivalent to A2-50	



- Flat head bolt with a pin at the center of the hexalobular socket \*1.
- This prevents mounting and removing with regular
- Install and remove with **SRX** Dedicated Wrench or **SRXB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.
- \*1: The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

## Application


Equipment/devices disassembly/tampering prevention Theft prevention for outdoor facilities Security measures Safety measures

																		Unit:mm
M (Coarse)													Applicable	Applicab	le Bit Type	Hexalobular		Otv
Part Number 1	Nominal of Thread	Pitch	L◀	<b>D</b> 1		D1	L1	Wrench Type	Bit		Socket No.	Mass (g)	Qty per Pack					
SRFXS-M3	M3	0.5	6	8	10	12					6	1.75	SRX-10	SRXB-10	SRD-6.35	10	0.48 - 0.72	10
SRFXS-M4	M4	0.7		8	10	12	16	20			8	2.3	SRX-20	SRXB-20	SRD-6.35	20	1 -1.9	10
SRFXS-M5	M5	8.0		8	10	12	16	20	25		10	2.8	SRX-25	SRXB-25	SRD-6.35	25	1.9 - 3.9	10
SRFXS-M6	M6	1			10	12	16	20	25	30	12	3.4	SRX-30	SRXB-30	SRD-6.35	30	3.3 -7	10

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.


## • SRX Dedicated Wrench

			Unit:mm
Part Number	L <sub>1</sub>	L2	Mass (g)
SRX-10	60	20	3.7
SRX-20	67	23	8.2
SRX-25	70	25	11
SRX-30	81	28	20




### • SRXB Bit Part No.

Part Number	Mass (g)
SRXB-10	4.36
SRXB-20	4.57
SRXB-25	4.79
SRXB-30	5.50



#### SRD Dedicated Magnet Screwdriver

Unit:m										
Part Number	L	В	Mass (g)							
SRD-6.35	210	6.35	98							



### • Related Products

Washer for Flat Head Screw **SWAS-RW** is available.



# • Part Number Specification





NBK.

🕵 Cleanroom Wash & Packaging 🛛 🔐 Screw Length Adjustment 🗠 🚅 Vibration Resistant 📔 Modification process for captive use

Available / Add'l charge | Available / Add'l charge | Not Available






# SRBS Button Head Cap Screws with Hexalobular Socket and Pin











#### Material/Finish

SRBS Main Body Equivalent to SUS304 Strength Class Equivalent to A2-50



- Button head cap screws with a pin at the center of the hexalobular socket \*1.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRX** Dedicated Wrench or **SRXB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.
- \*1: The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

### Application


Equipment/devices disassembly/tampering prevention Theft prevention for outdoor facilities Security measures Safety measures

																							Unit:mm
	M (Coarse	·)	L <b>€2</b>														Applicable	Applicabl	le Bit Type	Havalahulan			Otv
Part Number 1	Nominal of Thread	Pitch													D1	11	Wrench Type			Hexalobular Socket No.	Mas	s (g)	Qty per Pack
SRBS-M3	M3	0.5	6	8	10	12	15	16	20	25					5.7	1.65	SRX-10	SRXB-10	SRD-6.35	10	0.48	1.4	20
SRBS-M4	M4	0.7	6	8	10	12	15	16	20	25	30	35	40		7.6	2.2	SRX-20	SRXB-20	SRD-6.35	20	1.1	4.2	20*1
SRBS-M5	M5	0.8		8	10	12	15	16	20	25	30		40		9.5	2.75	SRX-25	SRXB-25	SRD-6.35	25	1.8	- 6.4	20
SRBS-M6	M6	1		8	10	12	15	16	20	25	30		40	50	10.5	3.3	SRX-30	SRXB-30	SRD-6.35	30	3	-12	10
SRBS-M8	M8	1.25			10	12		16	20	25	30		40	50	14	4.4	SRX-40	SRXB-40	SRD-6.35	40	7.3	- 22	10

- \*1: Quantity per pack for **SRBS-M4-35** and **SRBS-M4-40** is 1.
- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.


## • SRX Dedicated Wrench

			OHIL HIH
Part Number	L1	L2	Mass (g)
SRX-10	60	20	3.7
SRX-20	67	23	8.2
SRX-25	70	25	11
SRX-30	81	28	20
SRX-40	88	31	32




## • SRXB Bit Part No.

Part Number	Mass (g)
SRXB-10	4.36
SRXB-20	4.57
SRXB-25	4.79
SRXB-30	5.50
SRXB-40	6.00



# • SRD Dedicated Magnet Screwdriver

	Unit:mm		
Part Number	L	В	Mass (g)
SRD-6.35	210	6.35	98



• Part Number Specification





NBK.

🚫 Cleanroom Wash & Packaging 🔐 Screw Length Adjustment 🚅 Vibration Resistant ᆣ Modification process for captive use

Available / Add'l charge | Available / Add'l charge | Available / Add'l charge




# **SRSHS** Tamper Resistant Cap Screws with Ultra Low Profile











## Material/Finish

	₩ KUN3
	SRSHS
Main unit	SUSXM7



- Tamper resistant screws with head height of 1.5mm or less.
- This prevents mounting and removing with regular tools. The low head height makes it difficult to remove the screws by grasping the head itself, making them excellent for theft prevention.
- After mounting these do not protrude by much, so they do not affect the appearance.
- Install and remove with **SRSHB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.
- Application


Dismantling equipment/device, tamper-resistance/anti-theft measures for outdoor facility/ security measures/safety measures


															Unit:mm
Part Number	M (Coarse)		L <b>1</b>		D. 1	D1 L1	Bit Part No.	Applicable Screwdriver		Qty					
rait Number	Nominal of Thread	Pitch	L Z							וט	per Pack				
SRSHS-M2	M2	0.4	4	5	6	8				3	0.6	SRSHB-0	SRD-6.35	0.089 - 0.16	10
SRSHS-M2.5	M2.5	0.45	4	5	6	8				3.8	0.8	SRSHB-1	SRD-6.35	0.15 - 0.28	10
SRSHS-M3	M3	0.5			6	8	10	12		6	1.3	SRSHB-2	SRD-6.35	0.44 - 0.69	20
SRSHS-M4	M4	0.7				8	10	12	16	8	1.5	SRSHB-3	SRD-6.35	1 - 1.6	20

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

## • SRSHB Dedicated bit (Supports V6.3/U6.3 insert shapes)

Part Number Mass(g) SRSHB-0 2 6.4 SRSHB-1 6.4 SRSHB-2 13.8 SRSHB-3 4 14.7





• SRD Dedic	Unit:mm		
Part Number	L	В	Mass (g)
SRD-6.35	210	6.35	98

