




Seizing Prevention



Chemical-proof



SUS Stainless steel



● Material/Finish




	SNSS-TF
Main Body	SUSXM7 (S.S. Grade : A2) PTFE(Polytetrafluoroethylene) Coating
Strength Class	A2-70

● Tightening property (reference)

Part Number : SNSS-M5 - 25-TF

→ P.xxxx



- Excellent chemical resistance.
- The coating has excellent lubricating ability and is suitable for prevention of seizing.
- Complies with JIS B 1176, ISO 4762, and DIN 912. For details on shape and dimensions, please refer to the "Technical Information (JIS B 1176, ISO 4762)".

● Application

Seizing prevention. FPD production equipment, semiconductor devices, printed circuit board etching devices, metallic surface treatment equipment and facilities, and chemical plants

Unit : mm

Part Number	M (Coarse)		L 													D1	L1	B	Mass (g)
	Nominal of Thread 	Pitch																	
SNSS-M3-TF	M3	0.5	5	6	8	10	12	16	20						5.5	3	2.5	0.67 - 1.4	
SNSS-M4-TF	M4	0.7		6	8	10	12	16	20	25					7	4	3	1.5 - 3.2	
SNSS-M5-TF	M5	0.8			8	10	12	16	20	25					8.5	5	4	2.5 - 4.8	
SNSS-M6-TF	M6	1				10	12	16	20	25	30				10	6	5	4.7 - 8.3	
SNSS-M8-TF	M8	1.25						16	20	25	30	35			13	8	6	12 - 19	
SNSS-M10-TF	M10	1.5							20	25	30	35	40		16	10	8	23 - 33	

● Part number specification

SNSS - M6 - 25 - TF

Product Code



Product Code

Individual Sales → P.xxxxx	Cleanroom Wash & Packaging → P.xxxxx	Screw Length Adjustment → P.xxxxx	Vibration Resistant → P.xxxxx	Modification process for captive use → P.xxxxx
1 piece in 1 pack	Available / Add'l charge	Not Available	Not Available	Please feel free to contact us