




# SPE-R Plastic Socket Head Tapered Screw Plugs - PEEK

Heat-resistance Chemical-proof Electrical Insulation



## Material/Finish



	<b>SPE-R</b>
Main Body	PEEK (Polyether Ether Ketone) (Light Brown)
Heat Resistance Temperature*1	260°C

\*1: This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

- PEEK hex socket tapered screw plugs.
- PEEK is a thermoplastic super engineering plastic superior in physical and chemical properties.
- Excellent chemical resistance. It remains almost unaffected by chemicals other than concentrated sulfuric acid, concentrated nitric acid, and concentrated hydrofluoric acid.
- With excellent heat resistance and water resistance, it retains strength at high temperatures.
- It features outstanding resistance to wear, shock, and fatigue.
- It also has high flame retardance which clears the UL 94 V-0 standard.
- For the properties and precautions for use of plastic screws, see "Properties of Plastic Screws."

## Application

FPD production equipment / Semiconductor manufacturing equipment / Printed circuit board etching devices / Metallic surface treatment equipment and facilities / Chemical plants / Transformers / Electrical and electronic equipment / Hot water pumps / Chemical pumps

Unit : mm

Part Number	R (PT) Nominal of Thread	L	B	Mass (g)	Qty per Pack
<b>SPE-1-R</b>	R1/8	8	5	0.45	5
<b>SPE-1-R(100)</b>	R1/8	8	5	0.45	100
<b>SPE-2-R</b>	R1/4	11	6	1.1	5
<b>SPE-2-R(100)</b>	R1/4	11	6	1.1	100
<b>SPE-3-R</b>	R3/8	12	8	2.1	5
<b>SPE-3-R(100)</b>	R3/8	12	8	2.1	100

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

## Part Number Specification

### SPE-2-R



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available