


**SUS** Stainless steel



\*1: Setscrew head shapes have been changed from hex sockets to hexalobular sockets.

### Material/Finish



	LECM Made of Steel	LECMS Made of Stainless Steel
Lever Part	Nylon 6 (Various Color)	Nylon 6 (Various Color)
Thread Part	SUM22L Ferrosoferric Oxide Film (Black)	SUS303
Setscrew	Steel Ferrosoferric Oxide Film (Black)	Stainless Steel
Serration Ring	Zinc Die Cast	Zinc Die Cast
Spring	Stainless Steel Wire or SWPB	Stainless Steel Wire



- The product development was conducted with LCA, Life Cycle Assessment, in consideration for environmental load, especially for global warming.
- Greenhouse effect gas emission is reduced by 6.5 % compared to conventional products.
- A serration ring made of zinc die cast is inserted into the lever body made of plastic. They also realize sufficient strength for fitting with metal thread serration.
- Female screw type **LECF** **LECFs** with the same shape is available. ➔ P.xxxx
- There are five color variations. They can be selected by the end symbol of the part number.

End Symbol	Lever Part Color
<b>BK</b>	Matte black
<b>SG</b>	Matte Silver
<b>OR</b>	Matte orange
<b>YW</b>	Matte yellow
<b>SK</b>	Matte Transparent

### Part number specification

#### LECMS-3-16-SK

1 2 3

For 2 screw length Lm, select from the sizes marked with ● in the table.

## Dimensions

Unit : mm

Part Number	Part Number	M (Coarse)		R	H	H'	h	s	D	d	Number of Teeth	Max. load*1 (N)	Max. clamping force*1 (kN)	Mass (g)
Screw : Steel	Screw : Stainless steel	Nominal of Thread	Pitch											
<b>LECM-3</b>	<b>LECMS-3</b>	M3	0.5	30	29	32.5	24.5	4.2	13	10	18	13	0.95	14 - 15
<b>LECM-4</b>	<b>LECMS-4</b>	M4	0.7	30	29	32.5	24.5	4.2	13	10	18	31	1.7	15 - 16
<b>LECM-5</b>	<b>LECMS-5</b>	M5	0.8	30	29	32.5	24.5	4.2	13	10	18	62	2.7	16 - 20
<b>LECM-6</b>	<b>LECMS-6</b>	M6	1	30	29	32.5	24.5	4.2	13	10	18	110	3.8	16 - 22

\*1: For the definitions of maximum load and maximum clamping force, see "Using the Clamp Lever / Tension Lever."

**LECM** Thread part : made of steel **LECMS** Thread part : made of stainless steel

Part Number	Lm (mm)									
	6	8	10	12	16	20	25	32	40	50
<b>LECM-3</b>	●	●	●	●	●	●	●	●	●	●
<b>LECM-4</b>			●	●	●	●	●	●	●	●
<b>LECM-5</b>			●	●	●	●	●	●	●	●
<b>LECM-6</b>				●	●	●	●	●	●	●
<b>LECMS-3</b>	●	●	●	●	●	●	●	●	●	●
<b>LECMS-4</b>			●	●	●	●	●	●	●	●
<b>LECMS-5</b>			●	●	●	●	●	●	●	●
<b>LECMS-6</b>				●	●	●	●	●	●	●

Cleanroom Wash & Packaging ➔ P.xxxx	Screw Combination ➔ P.xxxx	Screw Length Adjustment ➔ P.xxxx	Vibration Resistant ➔ P.xxxx	Laser Marking ➔ P.xxxx
Please feel free to contact us	Not Available	Available / Add'l charge	Not Available	Available / Add'l charge