




# SNPX-TZB Hexalobular Socket Pan Head Machine Screws



## Material/Finish



	SNPX-TZB
Main Body	Steel Trivalent Chromate Treatment
Strength Class	4.8 Equivalent

- Hexalobular socket shapes\*1 are designed to withstand high tightening torque compared to cross-recesses.
- Recesses are unlikely to be damaged due to tightening, allowing safe and secure tightening to be performed.

\*1 : The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

## Application

Prevention of damage to screw heads  
Reliable tightening

Unit : mm

Part Number ◀1	M (Coarse)		L ◀2							D1	L1	Hexalobular Socket No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	6	8	10	12	16	20	25					
SNPX-M3-TZB	M3	0.5	6	8	10					5.5	2	10	0.51 - 0.66	20
SNPX-M4-TZB	M4	0.7	6	8	10	12	16	20	25	7	2.6	20	0.91 - 2.3	20
SNPX-M5-TZB	M5	0.8		8	10	12	16	20	25	9	3.3	25	2.2 - 4.1	20
SNPX-M6-TZB	M6	1			10	12	16	20	25	10.5	3.9	30	3.6 - 6.2	20

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

## Related Products

**SKX** Hexalobular Wrench



**SKX-N** Hexalobular Wrench for Extremely Limited Access Spaces



**SKXB** Hexalobular Short Bit



**SRD** Magnet Screwdriver



## Part Number Specification

**SNPX-M5-20-TZB**

◀1      ▶2      ▶1

1 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available