




SPC-TS Plastic Slotted Socket Set Screws - PC

Lightweight Electrical Insulation



- PC (polycarbonate) hex socket set screws. The slot makes it possible to choose tools in accordance with the application or work environment.
- PC (polycarbonate) has the highest shock resistance of engineering plastics.
- Allowable operating temperature*1 (min./max.): -40°C/115°C
- PC has low water absorbency and excellent weather resistance.
- For the properties and precautions for use of plastic screws, see "Properties of Plastic Screws."

Application

Electrical and electronic equipment

Material/Finish



	SPC-TS
Main Body	PC (Polycarbonate) (Transparent)
Heat Resistance Temperature*1	115°C

*1: This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

Unit : mm


Part Number	M (Coarse)		L					L1	B	t	a	Torsional Torque*1 (N·m)	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch												
SPC-M3-TS	M3	0.5		5	6	8	10	0.9	0.9	2.6	0.4	0.18	0.06 - 0.1	50
SPC-M3-TS(1000)	M3	0.5		5	6	8	10	0.9	0.9	2.6	0.4	0.18	0.06 - 0.1	1000
SPC-M4-TS	M4	0.7	4	5		8	10	1.2	1.3	3.2	0.6	0.39	0.09 - 0.14	50
SPC-M4-TS(1000)	M4	0.7	4	5		8	10	1.2	1.3	3.2	0.6	0.39	0.09 - 0.14	1000

*1: Values in chart are for reference only. They are not guaranteed values. The recommended tightening torque is 50% of the torsional torque.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Part Number Specification

SPC-M3-8-TS



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available	Not Available