

Material/Finish

	SRHFS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50



- Flat head bolts with pin at the center of their socket.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRH** Dedicated Wrench or **SRHB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.

Application

Machinery / Tools / Equipment / Devices disassembly prevention/ Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures


Part Number	M (Coarse)		L												D1	L1	B	Applicable Wrench Type	Applicable Bit Type		Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	6	8	10	12	16	20	25	30	35	40	50						Bit	Driver		
SRHFS-M3	M3	0.5	6	8	10	12	16	20	25						6	1.75	2	SRH-2	SRHB-2	SRD-6.35	0.53 - 1.4	10
SRHFS-M4	M4	0.7		8	10	12	16	20	25	30					8	2.3	2.5	SRH-2.5	SRHB-2.5	SRD-6.35	1.2 - 2.9	10
SRHFS-M5	M5	0.8		8	10	12	16	20	25	30		40	50		10	2.8	3	SRH-3	SRHB-3	SRD-6.35	2.3 - 7.4	10
SRHFS-M6	M6	1			10	12	16	20	25	30	35	40	50		12	3.4	4	SRH-4	SRHB-4	SRD-6.35	3.9 - 12	10
SRHFS-M8	M8	1.25			10	12	16	20	25	30	35	40	50		16	4.7	5	SRH-5	SRHB-5	SRD-6.35	9 - 23	10
SRHFS-M10	M10	1.5							25	30		40			18.3	5.6	6	SRH-6	SRHB-6	SRD-6.35	19 - 29	10

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

SRH Dedicated Wrench

Unit : mm


Part Number	B	L1	L2	Mass (g)
SRH-2	2	50	16	1.8
SRH-2.5	2.5	56	18	3.1
SRH-3	3	63	20	5
SRH-4	4	70	25	10
SRH-5	5	80	28	18
SRH-6	6	90	32	35



SRHB Bit Part No.

Unit : mm


Part Number	B	Mass (g)
SRHB-2	2	4.81
SRHB-2.5	2.5	4.93
SRHB-3	3	4.85
SRHB-4	4	6.31
SRHB-5	5	5.51
SRHB-6	6	5.98



SRD Dedicated magnet screwdriver

Unit : mm

Part Number	L	B	Mass (g)
SRD-6.35	210	6.35	98




Part number specification

SRHFS-M5 - 16

1

2



● Material/Finish

	SRHS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50



- Button head cap screws with pin at the center of their socket.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRH** Dedicated Wrench or **SRHB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.

● Application

Equipment/devices disassembly/tampering prevention
Theft prevention for outdoor facilities
Security measures
Safety measures


Part Number	M (Coarse)		L								D1	L1	B	Applicable Wrench Type	Applicable Bit Type		Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	6	8	10	12	16	20	25	30					Bit	Driver		
SRHS-M3	M3	0.5	6	8	10	12	16				5.7	1.65	2	SRH-2	SRHB-2	SRD-6.35	0.48 - 0.93	20
SRHS-M4	M4	0.7	6	8	10	12	16	20			7.6	2.2	2.5	SRH-2.5	SRHB-2.5	SRD-6.35	1.1 - 2.2	20
SRHS-M5	M5	0.8		8	10	12	16	20			9.5	2.75	3	SRH-3	SRHB-3	SRD-6.35	1.8 - 3.3	20
SRHS-M6	M6	1			10	12	16	20	25		10.5	3.3	4	SRH-4	SRHB-4	SRD-6.35	3.3 - 6.1	10

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● **SRH** Dedicated Wrench

Unit : mm


Part Number	B	L1	L2	Mass (g)
SRH-2	2	50	16	1.8
SRH-2.5	2.5	56	18	3.1
SRH-3	3	63	20	5
SRH-4	4	70	25	10



● **SRHB** Bit Part No.

Unit : mm


Part Number	B	Mass (g)
SRHB-2	2	4.81
SRHB-2.5	2.5	4.93
SRHB-3	3	4.85
SRHB-4	4	6.31



● **SRD** Dedicated Magnet Screwdriver


Unit : mm

Part Number	L	B	Mass (g)
SRD-6.35	210	6.35	98



● Part Number Specification

SRHS-M5-16



1 Individual Sales	 Cleanroom Wash & Packaging	 Screw Length Adjustment	 Vibration Resistant	 Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge