


# MOR Flexible Coupling - Oldham Type - Set Screw Type

High torque Electrical Insulation High Allowable Misalignment Small Eccentric Reaction Force

MOR



\*1: In a case where the bore diameter is  $\phi$  4 or less, the set screw is used in only one place.

## Dimensions

Unit : mm

Part Number	A	L	W	E	F	M	Screw Tightening Torque (N·m)
MOR-6	6	2.5	8.4	2.1	1.3	M2	0.18
MOR-8	8	2.5	9.6	3.1	1.3	M2	0.18
MOR-10	10	2.9	10.4	4.1	1.4	M2	0.18
MOR-12	12	3.9	14.4	5.2	2	M3	0.7
MOR-15	15	4.4	16	8.2	2.2	M3	0.7
MOR-17	17	4.9	19.7	8.2	2.5	M3	0.7
MOR-20	20	5.8	21.6	12.2	2.9	M3	0.7
MOR-26	26	7.3	25.6	14.2	3.7	M4	1.7
MOR-30	30	10	32.6	16.2	5	M4	1.7
MOR-34	34	11.1	34	16.2	5.6	M5	4
MOR-38	38	12.1	40.1	20.3	6.1	M5	4
MOR-45	45	13.8	46	22.3	6.9	M6	7
MOR-55	55	18.7	57	26.5	9.4	M8	15
MOR-68	68	24	77	38.5	12	M10	30

Unit : mm

Part Number	Standard Metric Bore Diameter (dimensional allowance H8)																							
	D1 · D2		2	3	4	5	6	6.35	8	9.525	10	12	14	15	16	18	20	22	25	28	30	35	38	
MOR-6	●	●	●																					
MOR-8	●		●	●																				
MOR-10			●	●	●																			
MOR-12				●	●	●																		
MOR-15					●	●	●	●	●															
MOR-17					●	●	●	●	●															
MOR-20					●	●	●	●	●	●														
MOR-26						●	●	●	●	●	●													
MOR-30							●	●	●	●	●	●												
MOR-34								●	●	●	●	●	●											
MOR-38									●	●	●	●	●	●										
MOR-45										●	●	●	●	●	●	●								
MOR-55											●	●	●	●	●	●	●	●						
MOR-68													●	●	●	●	●	●	●	●	●	●	●	●

Unit : inch

Part Number	Standard Inch Bore Diameter (dimensional allowance H7)						
	D1 · D2		2	3	4	5	6
	1 / 4	5 / 16	3 / 8	1 / 2	5 / 8	3 / 4	7 / 8
MOR-15	●		●				
MOR-17	●		●				
MOR-20	●		●	●			
MOR-26	●		●	●	●		
MOR-30				●	●		
MOR-34				●	●	●	
MOR-38				●	●	●	●
MOR-45					●	●	●
MOR-55						●	●

- All products are provided with hex socket set screws.
- Recommended tolerance for shaft diameters is h6 and h7.
- A set of hubs with set screw type for one side and clamping type for the other side and others are available upon request.
- For the shaft insertion amount to the coupling, see Mounting/maintenance.

• Part number specification

**MOR-15-5-6** 1 Set



**MOR-20 - SPCR** Single Spacer

Product Code Outside Diameter (A Dimension) Single Spacer

Additional Keyway at Shaft Hole → P.xxxx Cleanroom Wash & Packaging → P.xxxx Change to Stainless Steel Screw → P.xxxx

# MOR Flexible Coupling - Oldham Type - Set Screw Type

High torque  Electrical Insulation  High Allowable Misalignment  Small Eccentric Reaction Force 


## Performance

Part Number	Max. Bore Diameter (mm)	Keyway Additional Modification Max. Bore Diameter (mm)	Rated Torque *1 (N·m)	Maximum Torque *1 (N·m)	Max. Rotational Frequency (min <sup>-1</sup> )	Moment of Inertia (kg·m <sup>2</sup> )	Static Torsional Stiffness (N·m/rad)	Max. Lateral Misalignment (mm)	Max. Angular Misalignment (°)	Mass *2 (g)
<b>MOR-6</b>	2	—	0.2	0.4	100000	$2.2 \times 10^{-9}$	5	0.5	3	0.4
<b>MOR-8</b>	3	—	0.5	1	78000	$7.4 \times 10^{-9}$	12	0.7	3	0.8
<b>MOR-10</b>	4	—	0.8	1.6	63000	$1.9 \times 10^{-8}$	23	0.9	3	1
<b>MOR-12</b>	5	—	1	2	52000	$5.3 \times 10^{-8}$	60	1	3	3
<b>MOR-15</b>	8	8	1.6	3.2	42000	$1.4 \times 10^{-7}$	80	1	3	4
<b>MOR-17</b>	8	8	2.2	4.4	37000	$2.8 \times 10^{-7}$	120	1.2	3	7
<b>MOR-20</b>	12	12	3.2	6.4	31000	$5.7 \times 10^{-7}$	120	1.2	3	9
<b>MOR-26</b>	14	14	6	12	24000	$2.1 \times 10^{-6}$	300	1.5	3	20
<b>MOR-30</b>	16	16	15	30	21000	$5.4 \times 10^{-6}$	530	2	3	38
<b>MOR-34</b>	16	16	16	32	18000	$9.1 \times 10^{-6}$	1000	2.5	3	52
<b>MOR-38</b>	20	20	28	56	16000	$1.6 \times 10^{-5}$	1500	2.5	3	69
<b>MOR-45</b>	22	22	30	60	14000	$3.3 \times 10^{-5}$	2400	3	3	110
<b>MOR-55</b>	26	26	45	90	11000	$1.0 \times 10^{-4}$	4100	4	3	230
<b>MOR-68</b>	38	38	80	160	9000	$3.7 \times 10^{-4}$	6400	4.5	3	430

•\*1: Values with no load fluctuation and rotation in a single direction. If there is large load fluctuation, or both normal and reverse rotation, select a size with some margin. If ambient temperature exceeds 30°C, be sure to correct the rated torque and max. torque with temperature correction factor shown in the following table. The allowable operating temperature of **MOR** is -20°C to 80°C.

•\*2: These are values with max. bore diameter.

### Comparison of rated torque



### Ambient Temperature / Temperature Correction Factor

Ambient Temperature	Temperature Correction Factor
-20°C to 30°C	1.00
30°C to 40°C	0.80
40°C to 60°C	0.70
60°C to 80°C	0.55