




SPC-W-WH Plastic Washers - PC

Lightweight Electrical Insulation



- PC (polycarbonate) washers.
- PC (polycarbonate) has the highest shock resistance of engineering plastics.
- Allowable operating temperature*1 (min./max.): -40°C/115°C
- PC has low water absorbency and excellent weather resistance.
- For the properties and precautions for use of plastic screws, see "Properties of Plastic Screws."

• Application

Electrical and electronic equipment

• Material/Finish



	SPC-W-WH
Main Body	PC (Polycarbonate) (White)
Heat Resistance Temperature*1	115°C

*1: This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

Unit : mm

Part Number	d	D	t	Nominal	Mass (g)	Qty per Pack
SPC-8-W-WH	8.5	18	1.6	8	0.57	50
SPC-8-W-WH(500)	8.5	18	1.6	8	0.57	500
SPC-10-W-WH	10.5	22	1.6	10	1.1	20
SPC-10-W-WH(500)	10.5	22	1.6	10	1.1	500
SPC-12-W-WH	13	24	2.5	12	0.43	20
SPC-12-W-WH(500)	13	24	2.5	12	0.43	500

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

• Part Number Specification

SPC-10-W-WH



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available