




SRWFS Triwing Flat Head Machine Screws

Tamper Resistance **SUS** Stainless steel



Material/Finish





	SRWFS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50



- This prevents mounting and removing with regular tools.
- Install and remove with **SRWB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.

Application

Machinery / Tools / Equipment / Devices disassembly prevention / Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

Unit : mm																			
Part Number 	M (Coarse)		L 											D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch																	
SRWFS-M2	M2	0.4	5	6	8									3.8	1.2	SRWB-1	SRD-6.35	0.16 - 0.21	10
SRWFS-M3	M3	0.5		6	8	10	12	16	20	25				5.5	1.65	SRWB-2	SRD-6.35	0.53 - 1.4	10
SRWFS-M4	M4	0.7		6	8	10	12	16	20	25	30			8.4	2.7	SRWB-4	SRD-6.35	1.1 - 2.9	10
SRWFS-M5	M5	0.8				10	12	16	20	25	30	40	50	9.3	2.7	SRWB-5	SRD-6.35	2.5 - 7.4	10
SRWFS-M6	M6	1				10	12	16	20	25	30	40	50	11.3	3.3	SRWB-6	SRD-6.35	3.9 - 12	10
SRWFS-M8	M8	1.25						16	20	25	30	40	50	15.8	4.65	SRWB-7	SRD-6.35	11 - 23	10

Unit : mm

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

SRWB Dedicated bit

Unit : mm


Part Number	L	B	Mass (g)
SRWB-1	25.4	6.35	4.7
SRWB-2	25.4	6.35	4.8
SRWB-4	25.4	6.35	5.2
SRWB-5	25.4	6.35	5.6
SRWB-6	25.4	6.35	6.2
SRWB-7	25.4	6.35	6.6

SRWB

SRD Dedicated magnet screwdriver

Unit : mm

Part Number	L	B	Mass (g)
SRD-6.35	210	6.35	98

SRD

Part number specification

SRWFS-M5-16




Individual Sales → P.0000	Cleanroom Wash & Packaging → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Modification process for captive use → P.0000
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available



SRWS Triwing Pan Head Machine Screws

Tamper Resistance **SUS** Stainless steel



- This prevents mounting and removing with regular tools.
- Install and remove with **SRWB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.

Application

Machinery / Tools / Equipment / Devices disassembly prevention / Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

Material/Finish



	SRWS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

Unit : mm

Part Number	M (Coarse)		L	D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch							
SRWS-M3	M3	0.5	6 8 10	5.6	1.8	SRWB-2	SRD-6.35	0.54 - 0.7	20
SRWS-M4	M4	0.7	8 10 12	8.2	2.9	SRWB-4	SRD-6.35	1.5 - 1.9	20
SRWS-M5	M5	0.8	10 12 16	9.5	3.4	SRWB-5	SRD-6.35	2.8 - 3.5	20

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

SRWB Dedicated Bit

Unit : mm

Part Number	L	B	Mass (g)
SRWB-2	25.4	6.35	4.8
SRWB-4	25.4	6.35	5.2
SRWB-5	25.4	6.35	5.6

SRWB




SRD Dedicated Magnet Screwdriver

Unit : mm

Part Number	L	B	Mass (g)
SRD-6.35	210	6.35	98

SRD



Part number specification

SRWS-M5-16



Individual Sales → P. xxxxx	Cleanroom Wash & Packaging → P. xxxxx	Screw Length Adjustment → P. xxxxx	Vibration Resistant → P. xxxxx	Modification process for captive use → P. xxxxx
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge